


## AXIAL MARKING UNIT



### WATCH THE VIDEO

Marking of metal sheathed tubular elements with rating, voltage, type number etc, directly after the reduction of the tube is desirable from production point of view. Marking the tubes without intermediate handling means less operation cost and less danger for mix-up of elements.

The axial marking unit is a device that may be installed in line with the roll reducing mill to mark the reduced heating element along the element (parallel to its length axis).

The unit makes use of interchangeable pressing steel type characters with data such as:  
V - W - etc.



## Index

|                                 |   |
|---------------------------------|---|
| GENERAL CHARACTERISTICS .....   | 3 |
| TECHNICAL CHARACTERISTICS ..... | 3 |
| ADVANTAGES .....                | 3 |
| AVAILABLE VERSIONS .....        | 4 |
| OPTIONS .....                   | 4 |



### GENERAL CHARACTERISTICS

The marking and supporting rolls are mounted in a frame attached to the roll reducing mill and can be mounted on old as well as new mills.

The tube with-drawing device is attached to the marking equipment instead of the end plate of the bearing box assembly.

The reduced tube is pushed through the marking device by the rolls of the reducing rolling mill. The tube is automatically marked by the round type-holder which rotates to the end of the marking and then idles.

The tube is supported by a backing roll when being marked, avoiding bending of the tube and ensuring the right pressure for the correct imprinting of the characters on the heating element.

When the tube has passed, the type-holder automatically returns to its starting position.

The marking pressure can be varied by sliding in the block with the characters' holder.

The character-holding roll is removable to allow for the assembly of the characters sequence.


Both rolls have an adjustable position, depending to the tube diameter, with micrometric adjustment.

### TECHNICAL CHARACTERISTICS

|                                     |     |               |
|-------------------------------------|-----|---------------|
| Number of characters (spaces)       | max | 65            |
| Set of characters (numbers/letters) |     | to be defined |
| Tube diameter                       | mm  | min 6; max 16 |
| Time for change of the type holder  | min | 2-3           |

### ADVANTAGES

- smooth operation in line with the roll reduction mill
- flexible for different tube diameters



**AVAILABLE VERSIONS**

|  | <b>One row</b>    | <b>Two opposite rows</b> |
|--|-------------------|--------------------------|
| <b>FIXED MARKING UNIT</b>  |                   |                          |
| The beginning of marking is in a fixed <b>position</b> with reference to the element end                     | Mod. 141/30.00000 | Mod. 141/40.00000        |
| <b>PROGRAMMABLE MARKING UNIT</b>   |                   |                          |
| The beginning of marking is in a programmable position – from 50 to 200 mm with reference to the element end | Mod. 142/30.00000 | Mod. 142/40.00000        |

**OPTIONS**

|                           |   |
|---------------------------|---|
| <b>Mod. 100.07.001.00</b> | Character holding roll 2 mm   |
| <b>Mod. 10A.07.001.00</b> | Character holding roll 1.5 mm                                       |
| <b>Mod. 141/31.000000</b> | Character holding roll 2 mm, complete with a set of characters      |
| <b>Mod. 141/32.000000</b> | Character holding roll 1.5 mm, complete with a set of characters    |
| <b>Mod. 142/30.000020</b> | Set of parts for a 2nd tube diameter for marking device Mod. 142/30 |
| <b>Mod. 142/40.000020</b> | Set of parts for a 2nd tube diameter for marking device Mod. 142/40 |

**MARKING CHARACTERS**

|                           |                            |
|---------------------------|----------------------------|
| <b>Mod. 000.06.002</b>    | Marking characters, 2 mm   |
| <b>Mod. 001.06.002</b>    | Marking characters, 1.5 mm |
| <b>Mod. 000.06.002.01</b> | Spacer characters 2 mm     |
| <b>Mod. 001.06.002.01</b> | Marking characters, 1.5 mm |